



Enclosed trolley with 5 platforms, Type: 5393



Order data

Order number	919882 5393
GTIN	4017976019178
Item class	96F

Description

Version:

Steel angle section construction with tubular pushing handle. End walls, 1 side wall and roof clad with 40×40×4 mm wire mesh, fully welded. Positive bar locking with pivoting handle and padlock. 1 fixed platform and 4 loose shelves of chipboard with beech grain surface. Intermediate shelves adjustable at 100 mm intervals. The bottom shelf is not adjustable. 2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings. TOTALSTOP central braking system on the castors.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated.**

Technical description

Platform area width	1200 mm
Total load capacity	750 kg
Height of shelf 2	582 mm

Material of loose shelf	Sandwich boards with beech-effect surface.
Number of castors with parking brake	2
Height	1792 mm
Width	1370 mm
Height of shelf 1	292 mm
Height of shelf 5	1482 mm
Material of wheel	TPE
Load capacity of each loose shelf	90 kg
Push handle	yes
Height of shelf 3	882 mm
Standard	EN 1757-3
Weight	175 kg
Wheel Ø	200 mm
Type	5393
Height of shelf 4	1182 mm
Number of fixed wheels without parking brake	2
Depth	845 mm
Platform area depth	780 mm
Height adjustment interval	100
Type of product	Enclosed trolley