

**Platform trolley, Type: 2502****Order data**

Order number	919800 2502
GTIN	4017976025025
Item class	96F

Description**Version:**

Welded steel sections and tubes, platform made of chipboard with beech grain effect surface. 2 fixed wheels and 2 castors (with parking brake) and TPE tyres, hubs with grooved ball bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Standard	EN 1757-3
Safe working load	600 kg
Height	990 mm
Material of wheel	TPE
Type	2502
Number of fixed wheels without parking brake	2

Platform area height	270 mm
Wheel Ø	200 mm
Weight	30 kg
Platform area width	1000 mm
Width	1125 mm
Number of castors with parking brake	2
Depth	709 mm
Platform area depth	700 mm
Type of product	Platform trolley