



Table trolley with 2 platforms, Type: 2496B



Order data

Order number	919868 2496B
GTIN	4017976249605
Item class	96F

Description

Version:

Welded steel construction,
2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings.
Steel plate platforms **flush** with the frame.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Standard	EN 1757-3
Weight	42 kg
Material of wheel	TPE
maximum load capacity	500 kg

Height of top shelf	860 mm
Depth	609 mm
Type	2496B
Height	860 mm
Load capacity of top shelf	200 kg
Width	737 mm
Platform area depth	600 mm
Number of castors with parking brake	2
Platform area width	600 mm
Number of fixed wheels without parking brake	2
Height of bottom shelf	228 mm
Wheel Ø	160 mm
Type of product	Table trolleys