



Table trolley with 3 platforms, Type: 2750



Order data

Order number	919840 2750
GTIN	4017976027500
Item class	96F

Description

Version:

Welded steel sections and tubes, platform made of chipboard with beech-effect finish, resting on an angle section steel frame, raised edge 12 mm high.

2 fixed wheels and 2 castors Ø 125 mm (with parking brake) and TPE tyres, hubs with grooved ball bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Standard	EN 1757-3
Height of bottom shelf	200 mm
Height	1040 mm
maximum load capacity	300 kg

Height of top shelf	820 mm
Material of wheel	TPE
Platform area depth	500 mm
Platform area width	850 mm
Height of middle shelf	510 mm
Number of castors with parking brake	2
Width	985 mm
Depth	511 mm
Type	2750
Number of fixed wheels without parking brake	2
Wheel Ø	125 mm
Weight	35 kg
Load capacity of top shelf	80 kg
Load capacity of middle shelf	80 kg
Type of product	Table trolleys