

**Folding trolley, Type: 3100****Order data**

Order number	919808 3100
GTIN	4017976031002
Item class	96F

Description**Version:**

Welded steel frame with folding handle, 2 fixed wheels and 2 castors (with parking brake). Pressed steel sheet platform with anti-slip coating glued on. Solid rubber tyres.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Height folded up	240 mm
Weight	12.5 kg
Platform area height	150 mm
Type	3100
Wheel Ø	100 mm

Depth folded up	495 mm
maximum load capacity	150 kg
Number of fixed wheels without parking brake	2
Width folded up	760 mm
Number of castors with parking brake	2
Platform area width	740 mm
Material of wheel	Solid rubber
Standard	EN 1757-3
Platform area depth	480 mm
Type of product	Folding trolley