



Table trolley with 3 platforms, Type: 2752



Order data

Order number	919840 2752
GTIN	4017976021317
Item class	96F

Description

Version:

Welded steel sections and tubes, platform made of chipboard with beech-effect finish, resting on an angle section steel frame, raised edge 12 mm high.

2 fixed wheels and 2 castors Ø 125 mm (with parking brake) and TPE tyres, hubs with grooved ball bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Load capacity of middle shelf	80 kg
Wheel Ø	125 mm
Material of wheel	TPE
Standard	EN 1757-3

Platform area width	1000 mm
Load capacity of top shelf	80 kg
Depth	611 mm
Platform area depth	600 mm
Weight	49 kg
Number of fixed wheels without parking brake	2
Height of bottom shelf	200 mm
Number of castors with parking brake	2
Height of top shelf	820 mm
Height	1040 mm
Width	1135 mm
Type	2752
maximum load capacity	300 kg
Height of middle shelf	510 mm
Type of product	Table trolleys