



## Table trolley with 2 platforms, Type: 2400B



### Order data

Order number	919868 2400B
GTIN	4017976524009
Item class	96F

### Description

**Version:**

Welded steel construction,  
2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings.  
Steel plate platforms **flush** with the frame.

**Standard:**

**EN 1757-3**

**Colour:**

Brilliant blue RAL 5007 **powder-coated**.

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

### Technical description

Material of wheel	TPE
Platform area depth	500 mm
Width	1047 mm
Load capacity of top shelf	200 kg
Wheel Ø	160 mm

Standard	EN 1757-3
Type	2400B
Number of fixed wheels without parking brake	2
Height of top shelf	860 mm
maximum load capacity	500 kg
Number of castors with parking brake	2
Depth	509 mm
Weight	45 kg
Height	860 mm
Height of bottom shelf	228 mm
Platform area width	850 mm
Type of product	Table trolleys