

**Folding trolley, Type: 3101****Order data**

Order number	919808 3101
GTIN	4017976031019
Item class	96F

Description**Version:**

Welded steel frame with folding handle, 2 fixed wheels and 2 castors (with parking brake). Pressed steel sheet platform with anti-slip coating glued on. Solid rubber tyres.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Wheel Ø	125 mm
Depth folded up	630 mm
Number of castors with parking brake	2
Number of fixed wheels without parking brake	2
Width folded up	920 mm

Weight	18.5 kg
Type	3101
maximum load capacity	250 kg
Height folded up	275 mm
Platform area height	185 mm
Platform area width	910 mm
Material of wheel	Solid rubber
Standard	EN 1757-3
Platform area depth	610 mm
Type of product	Folding trolley