

Garant
Screw-on toolholder, right-hand, Shank / insert size: 10/09mm


Order data

Order number	260706 10/09
GTIN	4045197937445
Item class	21T

Technical description

Functional width L_4	14.25 mm
Shank size	10 mm
Overall length L	70 mm
ISO code toolholder	SSSCR/L 1010E09
Head length L_1	21 mm
Pack of insert screws	269028 23
Insert size	9 mm
suitable indexable insert	SC.. 09T3..
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500