

**Garant**
**Screw-on toolholder, right-hand, Shank / insert size: 8/09mm**

**Order data**

Order number	260706 8/09
GTIN	4045197937452
Item class	21T

**Technical description**

Shank size	8 mm
suitable indexable insert	SC.. 09T3..
Overall length L	60 mm
Insert size	9 mm
Pack of insert screws	269028 23
ISO code toolholder	SSSCR/L 0808D09
Head length L <sub>1</sub>	21 mm
Functional width L <sub>4</sub>	13.25 mm
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle $\kappa$	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500