

**Folding trolley, Type: KW1****Order data**

Order number	919810 KW1
GTIN	4017976011325
Item class	96F

Description**Version:**

Welded steel frame with folding handle, 2 fixed wheels and 2 castors (with parking brake). Chipboard platform. TPE tyres, hubs with grooved ball bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Width folded up	815 mm
Type	KW1
Height folded up	285 mm
Platform area height	205 mm
maximum load capacity	250 kg

Number of fixed wheels without parking brake	2
Depth folded up	470 mm
Weight	15 kg
Number of castors with parking brake	2
Wheel Ø	125 mm
Platform area width	720 mm
Material of wheel	TPE
Standard	EN 1757-3
Platform area depth	450 mm
Type of product	Folding trolley