

Manual hydraulic drive with high-pressure hose in a sheet metal case



Order data

Order number	834700
GTIN	2050000995675
Item class	86C

Description

Version:

Manual hydraulic drive with pressure rating up to approx. 600 bar, with high-pressure hose (1000 mm long), and hydraulic cylinder (with 3/4 -16 UNF thread suitable for draw bolts No. 834070).

Punching power: For round sheet metal punches and swarf punches up to $\varnothing 80$ / thickness 3 mm / St 37 or larger for thinner and weaker materials. **Case LxWxH: 370x220x150 mm.**

Application:

For powering sheet metal punches.

Note:

When ordering the hydraulic drive, please order the **draw bolts No. 834070 necessary** for the round sheet metal punches!

Technical description

Case length	370 mm
Case width	220 mm
Case height	130 mm
Type of product	Hole and punch tool

Accessories

Draw bolt Ø draw boltsxoverall length 19X135 mm	833360 19X135
Hydraulic hose	833440
Draw bolts with disc for round sheet metal punches Type 2	834070 2
Draw bolts with disc for round sheet metal punches Type 1	834070 1
Spare parts set for hydraulic drive No. 834700 Type 1	833420 1
Spare parts set for hydraulic drive No. 834700 Type 3	833420 3
Draw bolts with disc for round sheet metal punches Type 3	834070 3
Draw bolt, individual Ø draw boltsxoverall length 9,5X75 mm	833410 9,5X75
Hydraulic cylinder	833430
Spare parts set for hydraulic drive No. 834700 Type 4	833420 4
Spare parts set for hydraulic drive No. 834700 Type 2	833420 2
Draw bolts with disc for round sheet metal punches Type 4	834070 4