



## Table trolley with 2 platforms up to 1200 kg, Type: 12402



### Order data

Order number	919865 12402
GTIN	4017976124025
Item class	96F

### Description

**Version:**

Welded steel and sections and tubes, platforms made of non-slip platform of marine plywood. 2 fixed wheels and 2 castors (with parking brake), high-grade resilient solid blue-grey rubber treadless tyres (200×50 mm), and hubs with roller bearings.

**Standard:**

**EN 1757-3**

**Colour:**

Brilliant blue RAL 5007 **powder-coated**.

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

### Technical description

Height of top shelf	925 mm
Platform area depth	700 mm
Depth	700 mm
Type	12402
Number of castors with parking brake	2
maximum load capacity	1200 kg

Load capacity of top shelf	500 kg
Wheel Ø	200 mm
Platform area width	1000 mm
Height of bottom shelf	283 mm
Number of fixed wheels without parking brake	2
Height	925 mm
Standard	EN 1757-3
Width	1210 mm
Weight	67 kg
Material of wheel	Resilient solid rubber
Type of product	Table trolleys