



Table trolley with 2 platforms, Type: 2402B



Order data

Order number	919868 2402B
GTIN	4017976524023
Item class	96F

Description

Version:

Welded steel construction,
2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings.
Steel plate platforms **flush** with the frame.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Number of castors with parking brake	2
maximum load capacity	600 kg
Wheel Ø	200 mm
Type	2402B
Number of fixed wheels without parking brake	2

Standard	EN 1757-3
Height of bottom shelf	270 mm
Platform area width	1000 mm
Material of wheel	TPE
Height	900 mm
Platform area depth	700 mm
Depth	709 mm
Weight	61 kg
Load capacity of top shelf	200 kg
Width	1197 mm
Height of top shelf	900 mm
Type of product	Table trolleys