



## Platform trolley with 4 platforms, Type: 8312



### Order data

Order number	919880 8312
GTIN	4017976083124
Item class	96F

### Description

**Version:**

Welded steel sections and tubes, end walls with vertical tube struts at 130 mm spacing. Platforms made of chipboard with beech grain surface. Intermediate shelves adjustable at 100 mm intervals. The bottom shelf is not adjustable. 2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings.

**Standard:**

**EN 1757-3**

**Colour:**

Brilliant blue RAL 5007 **powder-coated.**

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

### Technical description

Total load capacity	600 kg
Material of wheel	TPE
Platform area width	1000 mm

Type	8312
Height of shelf 2	669 mm
Number of fixed wheels without parking brake	2
Number of castors with parking brake	2
Height of shelf 4	1469 mm
Standard	EN 1757-3
Load capacity of each loose shelf	90 kg
Weight	83 kg
Width	1169 mm
Wheel Ø	200 mm
Height of shelf 1	269 mm
Push handle	yes
Height of shelf 3	1069 mm
Height	1800 mm
Height adjustment interval	100 mm
Depth	709 mm
Platform area depth	700 mm
Height adjustment interval	100 mm
Type of product	Platform trolley