



## Table trolley with 2 platforms, Type: 2403B



### Order data

Order number	919868 2403B
GTIN	4017976524030
Item class	96F

### Description

**Version:**

Welded steel construction,  
2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings.  
Steel plate platforms **flush** with the frame.

**Standard:**

**EN 1757-3**

**Colour:**

Brilliant blue RAL 5007 **powder-coated**.

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

### Technical description

Number of fixed wheels without parking brake	2
Number of castors with parking brake	2
Material of wheel	TPE
Depth	809 mm
Height	900 mm

Load capacity of top shelf	200 kg
Platform area depth	800 mm
Width	1397 mm
Platform area width	1200 mm
Height of bottom shelf	270 mm
Height of top shelf	900 mm
Wheel Ø	200 mm
maximum load capacity	600 kg
Type	2403B
Weight	78 kg
Standard	EN 1757-3
Type of product	Table trolleys