

**Table trolley with 2 platforms, Type: 2496****Order data**

Order number	919860 2496
GTIN	4017976502496
Item class	96F

Description**Version:**

Welded steel sections and tubes, platforms made of chipboard with beech grain effect surface. 2 fixed wheels and 2 castors (with parking brake), TPE tyres, and hubs with grooved ball bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Material of wheel	TPE
Width	737 mm
Standard	EN 1757-3
Height of bottom shelf	228 mm
Depth	609 mm

Load capacity of top shelf	200 kg
maximum load capacity	500 kg
Platform area width	600 mm
Number of castors with parking brake	2
Weight	32 kg
Wheel Ø	160 mm
Type	2496
Number of fixed wheels without parking brake	2
Height of top shelf	860 mm
Height	860 mm
Platform area depth	600 mm
Type of product	Table trolleys