



Table trolley with 2 platforms, Type: 4820



Order data

Order number	919870 4820
GTIN	4017976048208
Item class	96F

Description

Version:

Welded steel construction, **oil-tight trays**.

2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings. **Oil-tight trays** with **40 mm** high edge.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Number of castors with parking brake	2
Type	4820
Number of fixed wheels without parking brake	2
Material of wheel	TPE
maximum load capacity	400 kg

Width	1021 mm
Height	870 mm
Height of bottom shelf	207 mm
Load capacity of top shelf	200 kg
Weight	36 kg
Platform area width	850 mm
Wheel Ø	160 mm
Height of top shelf	829 mm
Standard	EN 1757-3
Platform area depth	500 mm
Depth	500 mm
Type of product	Table trolleys