

Ansell**Pair of gloves HyFlex® 11-801, Glove size: 11****Order data**

Order number	094351 11
GTIN	10076490491793
Item class	04P

Description**Version:**

HyFlex® series. Versatile gloves with nitrile foam coating for precise and general tasks. Offers a good balance between comfort, freedom of movement and hand protection. With Ansell zonz® Comfort Fit Technology™ to reduce hand fatigue. Öko-Tex® Standard 100.

With Nylon-Spandex material and silicone-free coating. free of latex.

Standard:

EN 388; EN ISO 21420

Antistatisch gemäß EN 1149.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

DMF-free	no
Accuracy of fit	very good
Glove size	11
Wet grip	medium

Material of coating	Nitrile
Touch sensitivity	very good
Oil grip	good
Heat protection	not available
Breathability	very good
silicone-free	no
Series	HyFlex®
Type of glove	Multi-purpose gloves
Protection category	Category II
Clothing standard	Oeko-Tex Standard 100
Contents	12
Glove characteristics	Silicone-free
Glove characteristics	Suitable for allergy sufferers
Glove characteristics	DMF-free
Glove characteristics	free of latex
EN 388	3131A
Backing material	Spandex nylon
Coating	Nitrile foam
Coating variant	The palms of the hands
Application range	All-round
Length	192 mm
Colour	black / grey
Weight	20,4 g
Knitted technology	15G
Application	reusable
Material	Nitrile foam
Cut protection class	A
Type of product	Multi-purpose gloves

