

**Garant**
**GARANT Power Tang 90° tangential high-performance shoulder mill, Weldon shank, Ø D / Z<sub>eff</sub>: 25/2mm**

**Order data**

Order number	215972 25/2
GTIN	4045197940070
Item class	210

**Technical description**

Number of effective inserts $Z_{\text{eff}}$	2
Overall length $L_{\text{tot}}$	112 mm
suitable indexable insert	LO.U0904..
Shank Ø $D_s$ h6	25 mm
Overhang $L_1$	54 mm
Cutting edge Ø $D_c$	25 mm
maximum cutting depth $a_{p\text{max}}$	39 mm
Pack of insert screws	219868 2 (8IP; 1.2 Nm)
Series	Power Tang
Number of indexable inserts	10
Shank type	Weldon shank
Setting angle $\kappa$	90 degrees
Milling application	Corner milling
Spacing of the cutters	unequal spacing
Through-coolant	yes

Tool exchange	PowerCard
Type of product	End / face mill

---

## Accessories

Torque screwdriver, fixed setting set torque 1,2 N·m	211750 1,2
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP