

**Garant**
**GARANT Power Tang 90° tangential high-performance shoulder mill, Weldon shank, Ø D / Z<sub>eff</sub>: 40/4mm**

**Order data**

Order number	215972 40/4
GTIN	4045197940094
Item class	210

**Technical description**

maximum cutting depth $a_{p\ max}$	47 mm
Number of effective inserts $Z_{\ eff}$	4
Overall length $L_{\ tot}$	131 mm
Shank $\varnothing D_s$ h6	32 mm
Overhang $L_1$	69 mm
Pack of insert screws	219868 2 (8IP; 1.2 Nm)
Cutting edge $\varnothing D_c$	40 mm
suitable indexable insert	LO.U0904..
Series	Power Tang
Number of indexable inserts	24
Shank type	Weldon shank
Setting angle $\kappa$	90 degrees
Milling application	Corner milling
Spacing of the cutters	unequal spacing
Through-coolant	yes

Tool exchange	PowerCard
Type of product	End / face mill

---

## Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
Torque screwdriver, fixed setting set torque 1,2 N·m	211750 1,2