

Garant
GARANT Power Tang 90° tangential high-performance shoulder mill, Weldon shank, Ø D / Z_{eff}: 32/3mm

Order data

Order number	215972 32/3
GTIN	4045197940087
Item class	210

Technical description

suitable indexable insert	LO.U0904..
Shank Ø D _s h6	32 mm
Cutting edge Ø D _c	32 mm
maximum cutting depth a _{p max}	47 mm
Overhang L ₁	69 mm
Number of effective inserts Z _{eff}	3
Overall length L _{tot}	131 mm
Pack of insert screws	219868 2 (8IP; 1.2 Nm)
Series	Power Tang
Number of indexable inserts	18
Shank type	Weldon shank
Setting angle κ	90 degrees
Milling application	Corner milling
Spacing of the cutters	unequal spacing
Through-coolant	yes

Tool exchange	PowerCard
Type of product	End / face mill

Accessories

Torque screwdriver, fixed setting set torque 1,2 N·m	211750 1,2
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP