



## Chamfer mill 45°, Weldon shank, Type: 4



### Order data

Order number	216625 4
GTIN	4045197940162
Item class	220

### Technical description

suitable indexable insert	SP..060304
Ø D	4 mm
Overhang L <sub>1</sub>	28 mm
Overall length L <sub>tot</sub>	80 mm
maximum chamfering Ø D <sub>max</sub>	10 mm
Pack of insert screws	219840 (8IP; 1.2 Nm)
Number of cutting edges Z	1
Shank Ø D <sub>s</sub> h6	12 mm
Shank type	Weldon shank
Chamfering angle reverse	45 degrees
Through-coolant	no
Type of product	Indexable end mill

### Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile  
8IP

674252 8IP

Torque screwdriver, fixed setting set torque 1,2 N·m

211750 1,2