



## Chamfer mill 45°, Weldon shank, Type: 11



### Order data

Order number	216625 11
GTIN	4045197940179
Item class	220

### Technical description

Overall length $L_{tot}$	80 mm
$\varnothing D$	11 mm
Shank $\varnothing D_s$ h6	12 mm
maximum chamfering $\varnothing D_{max}$	20 mm
Number of cutting edges Z	2
suitable indexable insert	SP..060304
Pack of insert screws	219840 (8IP; 1.2 Nm)
Overhang $L_1$	32 mm
Shank type	Weldon shank
Chamfering angle reverse	45 degrees
Through-coolant	no
Type of product	Indexable end mill

### Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile  
8IP

674252 8IP

Torque screwdriver, fixed setting set torque 1,2 N·m

211750 1,2