



Chamfer mill 45°, Weldon shank, Type: 12



Order data

Order number	216625 12
GTIN	4045197940186
Item class	220

Technical description

Pack of insert screws	219841 (15IP; 3.0 Nm)
maximum chamfering $\varnothing D_{\max}$	23.7 mm
Shank $\varnothing D_s$ h6	20 mm
suitable indexable insert	SP..09T308
Overall length L_{tot}	100 mm
$\varnothing D$	12 mm
Number of cutting edges Z	1
Overhang L_1	37 mm
Shank type	Weldon shank
Chamfering angle reverse	45 degrees
Through-coolant	no
Type of product	Indexable end mill

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile
15IP

674252 15IP

Torque screwdriver, fixed setting set torque 3,0 N·m

211750 3,0