



Chamfer mill 45°, Weldon shank, Type: 16



Order data

Order number	216625 16
GTIN	4045197940193
Item class	220

Technical description

Overall length L_{tot}	100 mm
Number of cutting edges Z	2
suitable indexable insert	SP..09T308
Overhang L_1	32 mm
$\varnothing D$	16 mm
maximum chamfering $\varnothing D_{max}$	28.8 mm
Shank $\varnothing D_s$ h6	16 mm
Pack of insert screws	219841 (15IP; 3.0 Nm)
Shank type	Weldon shank
Chamfering angle reverse	45 degrees
Through-coolant	no
Type of product	Indexable end mill

Accessories

Torque screwdriver, fixed setting set torque 3,0 N·m

211750 3,0