



ROTO-DRIVE deburrer with deburring head Ø 10.4



Order data

Order number	838605
GTIN	7290005395451
Item class	83G

Description

Version:

Handle with rotating, exchangeable deburring head. Easy to use due to crank system.

Application:

For easy deburring, chamfering or reworking of holes, external diameters, threads, and grooves.

Technical description

overall length	155 mm
Type of product	Deburrers

Accessories

Hole deburring head HSS 90°, with shank Deburring head Ø 3,2 mm	838610 3,2
Internal thread cleaning blade HSS	838710
Hole deburring head HSS 90°, with shank Deburring head Ø 20 mm	838610 20
Hole deburring head HSS 90°, with shank Deburring head Ø 10,4 mm	838610 10,4
External deburring head HSS for Ø 4–18 mm	838660

Hole deburring head, 90°, with shank HSS TiN coated Deburring head Ø 10,4 mm	838611 10,4
Hole deburring head HSS 90°, with shank Deburring head Ø 6,3 mm	838610 6,3
O-ring groove deburring blade HSS	838760