



Tipper truck RAL 5007 with discharge valve, Skip volume: 250l



Order data

Order number	919920 250
GTIN	4017976147017
Item class	96D

Description

Version:

Oil-tight welded skip, on bearings for tipping.

Skip edge folded over twice at the top.

Chassis with integral fork lift slots, standing area and tilt lock.

2 fixed wheels and 2 castors (with parking brake) with TPE tyres, hubs with grooved ball bearings.

TOTALSTOP - central braking system to EN 1757-3 fitted as standard to the castors.

Callout:

Discharge valve with sieve for separating liquids from solids.

Tipping action is operated manually.

For emptying using a forklift truck or when heavily loaded we recommend a self-tipper.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Technical description

Fork-lift fork socket pitch B	203 mm
Wheel Ø	200 mm
Internal dimension at intake: width	194 mm

Height	780 mm
Length	1359 mm
Number of castors with parking brake	2
Bucket length	1200 mm
welded oil-tight	yes
Bucket height	413 mm
Skip volume	250 l
Weight	70 kg
Bucket width	652 mm
Pull cord	no
with fork insertion slots	yes
Drain cock version	Delivery tap with sieve
Tipping prevention	yes
Filling edge height with rollers	780 mm
Tipping mechanism	manual
Width	713 mm
Fork insertion slots dimension A	194 mm
Internal dimension at intake: height	72 mm
Safe working load	750 kg
Fork insertion slots dimension D	72 mm
Fork insertion slots dimension C	603 mm
Number of wheels	4
Number of fixed wheels without parking brake	2
Material of wheel	TPE
Colour	brilliant blue RAL 5007
Standard	EN 1757-3
Type of product	Tilting containers

