

Tilting container with low overall height, painted, Skip volume: 750l



Order data

Order number	919955 750
GTIN	2050001937452
Item class	94B

Description

Version:

Tilting container **for solid materials** with **low overall height** and well-balanced centre of gravity. A pull cable allows the container to be tipped at any height.

The sheet steel body of the container has a strengthening profile around the edge and a sturdy base frame with slots for fork-lift forks. A catch prevents accidental slipping off or tipping.

Fork-lift slots internal dimensions A×D = 200×60 mm.

Colour:

Optional **paint finishes** light blue RAL 5012, yellow orange RAL 2000, fire red RAL 3000, 1 reseda green RAL 601, mouse grey RAL 7005.

Technical description

Width	1280 mm
Application range	for solids
Fork-lift fork socket pitch B	495 mm
Skip volume	750 l
Safe working load	1000 kg

Height	680 mm
Weight	139 kg
Length	1440 mm
Filling edge height	495 mm
Colour selection	RAL 5012, 2000, 3000, 6011, 7005
Type of product	Tilting containers

Accessories

Set of wheels for tilting containers and swarf containers, polyamide, 4 pieces Load capacity / wheel 450 kg	919970 450
---	------------