

**Tipper truck RAL 5007 with discharge valve, Skip volume: 450l****Order data**

Order number	919920 450
GTIN	4017976147024
Item class	96D

Description**Version:**

Oil-tight welded skip, on bearings for tipping.

Skip edge folded over twice at the top.

Chassis with integral fork lift slots, standing area and tilt lock.

2 fixed wheels and 2 castors (with parking brake) with TPE tyres, hubs with grooved ball bearings.

TOTALSTOP - central braking system to EN 1757-3 fitted as standard to the castors.

Callout:

Discharge valve with sieve for separating liquids from solids.

Tipping action is operated manually.

For emptying using a forklift truck or when heavily loaded we recommend a self-tipper.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated.**

Technical description

Fork-lift fork socket pitch B	203 mm
Length	1374 mm

Fork insertion slots dimension D	72 mm
Safe working load	750 kg
Fork insertion slots dimension C	603 mm
Bucket width	669 mm
Drain cock version	Delivery tap with sieve
Filling edge height with rollers	733 mm
Material of wheel	TPE
Pull cord	no
Skip volume	450 l
Height	1072 mm
Bucket height	708 mm
Width	730 mm
Number of fixed wheels without parking brake	2
welded oil-tight	yes
Tipping prevention	yes
Number of wheels	4
Fork insertion slots dimension A	194 mm
Internal dimension at intake: height	72 mm
with fork insertion slots	yes
Internal dimension at intake: width	194 mm
Weight	83 kg
Bucket length	1214 mm
Wheel Ø	200 mm
Tipping mechanism	manual
Number of castors with parking brake	2
Colour	brilliant blue RAL 5007
Standard	EN 1757-3
Type of product	Tilting containers

