

Tilting container with low overall height, painted, Skip volume: 1000l



Order data

Order number	919955 1000
GTIN	2050001937469
Item class	94B

Description

Version:

Tilting container **for solid materials** with **low overall height** and well-balanced centre of gravity. A pull cable allows the container to be tipped at any height. The sheet steel body of the container has a strengthening profile around the edge and a sturdy base frame with slots for fork-lift forks. A catch prevents accidental slipping off or tipping. Fork-lift slots internal dimensions $A \times D = 200 \times 60$ mm.

Colour:

Optional **paint finishes** light blue RAL 5012, yellow orange RAL 2000, fire red RAL 3000, 1 reseda green RAL 601, mouse grey RAL 7005.

Technical description

Length	1640 mm
Safe working load	1500 kg
Height	780 mm
Application range	for solids
Fork-lift fork socket pitch B	495 mm

Width	1280 mm
Weight	184 kg
Skip volume	1000 l
Filling edge height	565 mm
Colour selection	RAL 5012, 2000, 3000, 6011, 7005
Type of product	Tilting containers

Accessories

Set of wheels for tilting containers and swarf containers, polyamide, 4 pieces Load capacity / wheel 450 kg	919970 450
---	------------