



## Knurl forming tool right-hand, Shank size: 12mm



### Order data

Order number	290018 12
GTIN	4030741660689
Item class	29H

### Description

#### Version:

Grub screw in the shank for clearance angle correction.

Carbide roller pin for increased wear resistance.

- **Minimal pressure reduces stress on the workpiece and machine.**
- **Synchronising spindle for easy adjustment of knurl carriers and centre heights.**

### Technical description

Shank width	12 mm
Working range	0 - 15 mm
for knurl bore $\varnothing d_2$	4 mm
Roller pin	299910 6
for knurl $\varnothing d_1$	15 mm
Shank height	12 mm
for knurl width w	4 mm
for knurl profile	RAA 2×AA
for knurl profile	RBL 2×BR
for knurl profile	RGE45° BL/BR45°
for knurl profile	RAA 1×AA

for knurl profile

RBR 2×BL

Type of product

Self-centering knurling tool