



Knurl forming tool left-hand, Shank size: 16mm



Order data

Order number	290019 16
GTIN	4030741660740
Item class	29H

Description

Version:

Grub screw in the shank for clearance angle correction.

Carbide roller pin for increased wear resistance.

- **Minimal pressure reduces stress on the workpiece and machine.**
- **Synchronising spindle for easy adjustment of knurl carriers and centre heights.**

Technical description

Shank height	16 mm
for knurl $\varnothing d_1$	15 mm
Roller pin	299910 6
Shank width	16 mm
for knurl width w	4 mm
for knurl bore $\varnothing d_2$	4 mm
Working range	0 - 15 mm
for knurl profile	RAA 2×AA
for knurl profile	RBL 2×BR
for knurl profile	RBR 2×BL
for knurl profile	RAA 1×AA

for knurl profile

RGE45° BL/BR45°

Type of product

Self-centering knurling tool