

**Hole deburring head HSS 90°, with shank, Deburring head Ø: 16,5mm****Order data**

Order number	838610 16,5
GTIN	7290003239276
Item class	83G

Description**Application:**

For easy deburring and chamfering of holes with crank system for different materials, leaving a clean finish.

Suitable for:

Roto-Drive deburrers No. 838605 / 838611.

Technical description

Deburring head Ø	16.5 mm
Type of product	Blade