



ROTO-DRIVE deburrer with external deburring head Ø 4 - 18



Order data

Order number	838655
GTIN	7290005395444
Item class	83G

Description

Version:

Handle with rotating, exchangeable deburring head. Easy to use due to crank system.

Application:

For easy deburring, chamfering or reworking of holes, external diameters, threads, and grooves.

Technical description

overall length	155 mm
Type of product	Deburrers

Accessories

Hole deburring head, 90°, with shank HSS TiN coated Deburring head Ø 10,4 mm	838611 10,4
Hole deburring head HSS 90°, with shank Deburring head Ø 20 mm	838610 20
O-ring groove deburring blade HSS	838760
Internal thread cleaning blade HSS	838710
Hole deburring head HSS 90°, with shank Deburring head Ø 6,3 mm	838610 6,3

Hole deburring head HSS 90°, with shank Deburring head
Ø 10,4 mm

838610 10,4

Hole deburring head HSS 90°, with shank Deburring head
Ø 3,2 mm

838610 3,2

External deburring head HSS for Ø 4–18 mm

838660