

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 10/07mm


Order data

| | |
|--------------|---------------|
| Order number | 261346 10/07 |
| GTIN | 4045197941459 |
| Item class | 21T |

Technical description

| | |
|--|----------------|
| Overall length L | 100 mm |
| Minimum pre-drill $\varnothing D_{\min}$ | 12.5 mm |
| Neck width L_4 | 7.5 mm |
| Centre offset L_3 | 7 mm |
| ISO code toolholder | A10H SVLCR/L07 |
| suitable indexable insert | VC.. 0702.. |
| Clamping height L_2 | 9 mm |
| Head length L_1 | 22 mm |
| Pack of insert screws | 269028 27 |
| Setting angle κ | 95 degrees |
| Insert size | 7 mm |
| Usable depth T | 5 mm |
| Shank $\varnothing D_s$ | 10 mm |
| Standard | Works standard |
| Application type | right-hand |
| Boring depth up to | 3xD |
| Through-coolant | yes |

| | |
|-----------------|-------------------------------|
| Application | Internal longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|------------|
| Torque screwdriver with scale, to take D 6.3 bits maximum torque 200 cNm | 659905 200 |
| Bit for Torx®, 1/4 inch C 6.3, with torsion zone Torx® profile TX6 | 675155 TX6 |
| Torque screwdriver with scale, to take D 6.3 bits maximum torque 200 cNm | 659956 200 |