

Garant
Boring bar steel, right-hand, Shank \varnothing / insert size: 8/05mm


Order data

Order number	261352 8/05
GTIN	4045197941558
Item class	21T

Technical description

ISO code toolholder	A08F SVVCR/L05
Insert size	5 mm
Overall length L	80 mm
Neck width L ₄	6 mm
Pack of insert screws	269028 26
Centre offset L ₃	5.5 mm
Setting angle κ	72.5 degrees
suitable indexable insert	VC.. 0501..
Minimum pre-drill $\varnothing D_{\min}$	10.2 mm
Head length L ₁	15 mm
Clamping height L ₂	7.5 mm
Usable depth T	3,5 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX5	674248 TX5
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200