

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 12/07mm


Order data

Order number	261353 12/07
GTIN	4045197941572
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	15.5 mm
Overall length L	125 mm
Setting angle κ	72.5 degrees
Pack of insert screws	269028 27
suitable indexable insert	VC.. 0702..
Insert size	7 mm
Centre offset L_3	9 mm
Neck width L_4	9 mm
ISO code toolholder	A12K SVVCR/L07
Clamping height L_2	11 mm
Head length L_1	28 mm
Usable depth T	6 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200