



Chamfer mill 45°, Weldon shank, Type: 30



Order data

Order number	216625 30
GTIN	4045197941244
Item class	220

Technical description

Number of cutting edges Z	3
maximum chamfering $\varnothing D_{\max}$	42.3 mm
Overhang L_1	32 mm
suitable indexable insert	SP..09T308
Overall length L_{tot}	100 mm
Pack of insert screws	219841 (15IP; 3.0 Nm)
Shank $\varnothing D_s$ h6	20 mm
$\varnothing D$	30 mm
Shank type	Weldon shank
Chamfering angle reverse	45 degrees
Through-coolant	no
Type of product	Indexable end mill

Accessories

Torque screwdriver, fixed setting set torque 3,0 N·m

211750 3,0