

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 16/07mm

Order data

| | |
|--------------|---------------|
| Order number | 261353 16/07 |
| GTIN | 4045197941565 |
| Item class | 21T |

Technical description

| | |
|--|----------------|
| Head length L_1 | 36 mm |
| ISO code toolholder | A16M SVVCR/L07 |
| Setting angle κ | 72.5 degrees |
| Clamping height L_2 | 15 mm |
| Pack of insert screws | 269028 27 |
| suitable indexable insert | VC.. 0702.. |
| Minimum pre-drill $\varnothing D_{\min}$ | 19.5 mm |
| Overall length L | 150 mm |
| Centre offset L_3 | 11 mm |
| Insert size | 7 mm |
| Neck width L_4 | 12.9 mm |
| Usable depth T | 6 mm |
| Shank $\varnothing D_s$ | 16 mm |
| Standard | Works standard |
| Application type | left-hand |
| Boring depth up to | 3xD |
| Through-coolant | yes |

| | |
|-----------------|-------------------------------|
| Application | Internal longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|------------|
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6 | 674248 TX6 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm | 659957 200 |