

Garant
Boring bar, steel, left-hand, Shank \varnothing / insert size: 10/07mm

Order data

Order number	261347 10/07
GTIN	4045197941497
Item class	21T

Technical description

Overall length L	100 mm
ISO code toolholder	A10H SVLCR/L07
Neck width L ₄	7.5 mm
Centre offset L ₃	7 mm
suitable indexable insert	VC.. 0702..
Insert size	7 mm
Clamping height L ₂	9 mm
Head length L ₁	22 mm
Minimum pre-drill $\varnothing D_{\min}$	12.5 mm
Pack of insert screws	269028 27
Setting angle κ	95 degrees

Usable depth T	5 mm
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take D 6.3 bits maximum torque 200 cNm	659905 200
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Torque screwdriver with scale, to take D 6.3 bits maximum torque 200 cNm	659956 200