

Garant
Boring bar, steel, left-hand, Shank \varnothing / insert size: 16/07mm

Order data

Order number	261347 16/07
GTIN	4045197941510
Item class	21T

Technical description

Centre offset L_3	11 mm
Overall length L	150 mm
Minimum pre-drill $\varnothing D_{\min}$	19.5 mm
suitable indexable insert	VC.. 0702..
ISO code toolholder	A16M SVLCR/L07
Setting angle κ	95 degrees
Clamping height L_2	15 mm
Insert size	7 mm
Pack of insert screws	269028 27
Head length L_1	36 mm
Neck width L_4	14.5 mm

Usable depth T	5 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take D 6.3 bits maximum torque 200 cNm	659905 200
Bit for Torx®, 1/4 inch C 6.3, with torsion zone Torx® profile TX6	675155 TX6
Torque screwdriver with scale, to take D 6.3 bits maximum torque 200 cNm	659956 200