

Garant
Boring bar steel, right-hand, Shank \varnothing / insert size: 8/05mm


Order data

Order number	261338 8/05
GTIN	4045197941275
Item class	21T

Technical description

Insert size	5 mm
Centre offset L_3	3 mm
ISO code toolholder	A08F SVJCR/L05
Head length L_1	15 mm
Overall length L	80 mm
Pack of insert screws	269028 26
suitable indexable insert	VC.. 0501..
Minimum pre-drill $\varnothing D_{\min}$	8 mm
Clamping height L_2	7.5 mm
Neck width L_4	6 mm
Setting angle κ	142 degrees
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX5

674248 TX5

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200