

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 10/07mm


Order data

Order number	261339 10/07
GTIN	4045197941299
Item class	21T

Technical description

Centre offset L_3	1.5 mm
Minimum pre-drill $\varnothing D_{\min}$	13 mm
Clamping height L_2	9 mm
ISO code toolholder	A10K SVJCR/L07
Head length L_1	18 mm
Setting angle κ	142 degrees
Overall length L	125 mm
Neck width L_4	6.3 mm
suitable indexable insert	VC.. 0702..
Pack of insert screws	269028 27
Insert size	7 mm
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200