

Garant
Boring bar steel, right-hand, Shank \varnothing / insert size: 10/07mm

Order data

Order number	261352 10/07
GTIN	4045197941541
Item class	21T

Technical description

suitable indexable insert	VC.. 0702..
Minimum pre-drill $\varnothing D_{\min}$	13.5 mm
Insert size	7 mm
Neck width L_4	6.8 mm
Setting angle κ	72.5 degrees
Head length L_1	22 mm
Pack of insert screws	269028 27
Overall length L	100 mm
ISO code toolholder	A10H SVVCR/L07
Centre offset L_3	8 mm
Clamping height L_2	9 mm
Usable depth T	6 mm
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200