

**Garant**
**Boring bar steel, right-hand, Shank  $\varnothing$  / insert size: 12/07mm**

**Order data**

Order number	261352 12/07
GTIN	4045197941534
Item class	21T

**Technical description**

Centre offset $L_3$	9 mm
Clamping height $L_2$	11 mm
Head length $L_1$	28 mm
Setting angle $\kappa$	72.5 degrees
ISO code toolholder	A12K SVVCR/L07
Minimum pre-drill $\varnothing D_{\min}$	15.5 mm
Neck width $L_4$	9 mm
suitable indexable insert	VC.. 0702..
Overall length L	125 mm
Insert size	7 mm
Pack of insert screws	269028 27
Usable depth T	6 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200