

**Garant**
**Boring bar steel, left-hand, Shank  $\varnothing$  / insert size: 8/05mm**


## Order data

Order number	261339 8/05
GTIN	4045197941305
Item class	21T

## Technical description

Clamping height $L_2$	7.5 mm
Head length $L_1$	15 mm
suitable indexable insert	VC.. 0501..
Minimum pre-drill $\varnothing D_{\min}$	8 mm
ISO code toolholder	A08F SVJCR/L05
Overall length $L$	80 mm
Centre offset $L_3$	3 mm
Neck width $L_4$	6 mm
Setting angle $\kappa$	142 degrees
Insert size	5 mm
Pack of insert screws	269028 26
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

---

**Accessories**

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX5

674248 TX5

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200