

Tilting container with roller system, painted, Skip volume: 1200l



Order data

Order number	919950 1200
GTIN	2050001937421
Item class	94B

Description

Version:

Tilting container **for solid materials** with a well-balanced centre of gravity. A pull cable allows the container to be tipped at any height.

The sheet steel body of the container has a strengthening profile around the edge and a sturdy base frame with slots for fork-lift forks. A catch prevents accidental slipping off or tipping.

Fork-lift slots internal dimensions A×D = 200×80 mm.

Colour:

Optional **paint finishes** light blue RAL 5012, yellow orange RAL 2000, fire red RAL 3000, reseda green RAL 6011, mouse grey RAL 7005.

Technical description

Height	1095 mm
Fork-lift fork socket pitch B	600 mm
with pull cord	yes
Tipping prevention	yes
Application range	for solids

Skip volume	1200 l
Safe working load	1500 kg
Width	1070 mm
Weight	200 kg
Length	1720 mm
Filling edge height	960 mm
Colour selection	RAL 5012, 2000, 3000, 6011, 7005
Type of product	Tilting containers

Accessories

Set of wheels for tilting containers and swarf containers,
polyamide, 4 pieces Load capacity / wheel 450 kg

919970 450