

Garant**Pallet dolly, Platform area width×depth: 1200X800mm****Order data**

Order number	919908 1200X800
GTIN	4045197684196
Item class	91T

Description**Version:**

Sturdy steel angle section construction with 4 corner supports to take flat pallets and mesh crates. Resilient solid rubber tyres with 2 fixed wheels and 2 castors (with parking brake) and roller bearing hubs.

Application:

To take flat pallets and mesh crates.

Colour:

Silver **powder-coated.**

Technical description

Width	1275 mm
Number of fixed wheels without parking brake	2
Number of castors with parking brake	2
Platform area height	245 mm
Weight	36 kg
Wheel Ø	160 mm
Material of wheel	Resilient solid rubber
Safe working load	1200 kg
Height	300 mm
Platform area width	1210 mm

Platform area depth	810 mm
Depth	875 mm
Push handle	no
Type of product	Pallet mobility frame