



Screw-on toolholder set, right-hand, Shank / insert size: 25mm



Order data

Order number	255130 25
GTIN	4045197941732
Item class	29W

Technical description

Shank size	25 mm
Overall length L	150 mm
Series	QuickTurn
Head length L ₁	25 mm
ISO code toolholder	PCLNR 2525M16; PDJNR 2525M15; PSSNR 2525M12
Functional width L ₄	32 mm
suitable indexable insert	CN.. 1606.; DN.. 1506.; SN.. 1204..
Spare part	259981 3
Standard	DIN ISO 5610
Application type	right-hand
Application	External longitudinal turning
Application	External longitudinal turning

Type of product

Boring bar

Accessories

Spare parts set for lever lock toolholder Type 3	259981 3
Lever lock toolholder Shank / insert size 25/12 mm	251112 25/12
Lever lock toolholder Shank / insert size 25/15 mm	250610 25/15
Lever lock toolholder Shank / insert size 25/16 mm	250018 25/16